

FISHER & PAYKEL

DATA SHEET

600mm Double Integrated DishDrawer™

Model no: DD60DI9 DD60DHI9

Product Dimensions	mm
 Ø Overall height* of DishDrawer™ 	820 - 880
® Overall width** of DishDrawer™	599
© Depth of DishDrawer™ chassis**	553
 Ventilation gap between custom panels 	8
Height of chassis at rear (not including mounted feet)	811
 F Height of mounted feet (adjustable) 	9 - 69
 Height of toekick custom panel (adjustable) 	58 - 118
^(H) Depth from front of drawer panel to front of toekick panel***(adjustable)	40 - 100
③ Depth of drawer (open) (measured from front datum)**	527

* Includes adjustable mounted feet and the range of movement.

 ** Does not include the custom drawer panels, handles or toekick panel to be manufactured and fitted by cabinetmaker.

*** Assuming panel thickness of 18mm. If the toekick depth is greater than 50mm, the panel will need to be cut to clear the underside of the tub, please refer to the installation manual for more detail.

Note: Service outlet at rear extends both sides, hoses and cords can be routed to either or both.

Minimum Clearances	mm
Minimum inside height of cavity from bottom datum*	820
Minimum inside width of cavity	600
Minimum inside depth of cavity from front datum	560
Minimum ventilation gap between custom panels	8
minimum clearance from underside of bench to top of custom panel	2
Minimum clearance from bottom of toekick panel to floor	12
Minimum clearance from a corner cupboard	13

* Depending on adjustment of leveling feet.

DATE: 28.05.2018

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ±2mm (1/16"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com

0 100 200 400 millimetres

FISHER & PAYKEL

CUSTOM PANEL PREPARATION 600mm Double Integrated DishDrawer™

Model no: DD60DI9 DD60DHI9

Dimensions	mm
Minimum height of top drawer panel*	398
® Width of top drawer and bottom drawer panels	596 - 615
© Minimum height of bottom drawer panel*	311 - 360
• Height from floor to top of bottom drawer panel**	414 - 474
Ventilation gap between top drawer panel and bottom drawer panel	8
Height of toekick panel*	58 - 118
I Depth of custom panels	16 - 20

Maximum weight of each drawer panel (including handle)	
Maximum weight of each drawer panel (including handle)	9 kg

* The top drawer panel may be extended up, or the bottom panel down from the fixed gap between both. Adjust the height of the toekick panel accordingly.

** Depending on adjustment of leveling feet.

NOTE:

If the toekick depth is greater than 50mm, the panel will need to be cut to clear the underside of the tub, please refer to the installation manual and panel preparation downloads for more detail.



Ø

G

ß

A

G



PROFILE VIEW

DATE: 28.05.2018

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ±2mm (1/16"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com